

APOZA

TOP Selector

ULTRASONIC PIEZO SCALER & ENDODONTICS UNIT



THE VERY EXCELLENT ULTRASONIC SCALER.

CE
0120



TOP Selector

ULTRASONIC PIEZO SCALER & ENDODONTICS UNIT

SCALING FUNCTION:

TOP SELECTOR, a powerful piezoelectric scaler, provides stable ultrasonic oscillation of 33.5KHz with very wide energy scope.

- Titanium Handpiece is autoclavable
- Bring patients the most comfort with high power & frequency
- Suitable for long time operation without building heat.
- Easy to remove intractable calculus
- Fine tuning control on power supply and waterspray

ENDODONTIC FUNCTION:

Turn the power below half of **TOP SELECTOR** and replace tip with endo kit (Endo-holder+U-file) to operate unit for root canal treatment.

- Smoother canal grants better obturation
- Rapid and superior operation for root canal treatment
- Root canal enlargement and swirling irrigation for debridement
- Minimum dentin removal keeps integrity of the tooth structure.

SPECIFICATION:

Power supply	: AC230V~or 115V~(optional) 50/60Hz
Frequency	: 33.5± 1 KHz
Output power to Tip	: Operator adjustable from 20 to 40 watts
Weight	: 2kg (With handpiece)
Dimension	: W170 x D160 x H110 mm
Water pressure	: 1~4kg/cm ²
Fuse	: F0.5A(for 230V unit) F1A (for 115V unit)

Standard Package :

a. Handpiece (autoclavable)	X 1
b. Control Box	X 1
c. Scaling Tips (autoclavable)	X 3
d. Touque Wrench (autoclavable)	X 1
e. Foot Pedal	X 1
f. Electric Power Cable	X 1
g. Handpiece Box (autoclavable)	X 1

Accessories: Optional

- h. Tip No.1
- i. Tip No.2
- j. Tip No.3
- k. Tip No.5
- l. Endo Kit (1 Endo holder+1 Chuck + 6 X U-files)



APOZA
ENTERPRISE CO., LTD.

6F, 657, Chung-Cheng Road, Hsin-Chuang District, 242 New Taipei city, Taiwan, R.O.C.
Tel: 886-2-2901-0620
Fax: 886-2-2901-2208
<http://www.apoza.com>
e-mail: apoza@apoza.com.tw